

Fewer buttons, easier to operate. The halogen lamp has been replaced by a heat resistance inside the unit. There is also a fan for optimal drying. There is light for checking the spray samples as well. Connect the power and you are ready to go.

FINIXA @

DRYING OVEN FOR SPRAY SAMPLE PLATES

ILO 20

- Drying oven for spray samples
- Easy to use
- Can be used with water and solvent-based paints
- Just connect to the power supply

DIFFERENCES FROM LLO 10

- Uses a heat resistor instead of a halogen lamp and thus consumes less energy
- Built-in fan for better airflow and optimal drying
- Built-in light for checking the spray sample
- Easier to operate
- Requires only 220V power supply, no compressed air













